

Pneumatic muffler

U-1/4-20

Part number: 534223

FESTO



Data sheet

Feature	Value
Mounting position	Any
Pack size	20
Operating pressure	0 MPa...1 MPa 0 bar...10 bar
Flow rate with respect to atmosphere	3300 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Information on operating and pilot media	Operation with oil lubrication possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Noise level	76 dB(A)
Ambient temperature	-10 °C...70 °C
Product weight	7.7 g
Pneumatic connection	G1/4
Cushioning insert material	PE
Note on materials	RoHS-compliant