


Plug
FBS-SUB-9-GS-1X9POL-B
Part number: 534497

FESTO



Data sheet

Feature	Value
Width	20 mm
Height	62 mm
Length	61 mm
Product weight	60 g
Fieldbus interface	1x 9 spring-loaded terminals
Approved cable diameter	5 mm...10 mm
Degree of protection	IP65 IP67 In mounted state as per IEC 60529
Ambient temperature	0 °C...50 °C
Storage temperature	-20 °C...70 °C
Relative air humidity	95 % Non-condensing
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	PA-reinforced
Material of union nut	Brass
Material of screws	Steel
Seals material	NBR