

Compressed air filter MS12N-LF

Part number: 535026

FESTO



Data sheet

Feature	Value
Size	12
Series	MS
Mounting position	Vertical +/- 5°
Condensate drain	Fully automatic Fully automatic, electrically controlled Manual, non-detenting Manually rotating
Structural design	Sinter filter with centrifugal separator
Degree of condensate separation	75 %
Operating pressure	0.8 bar...20 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [::9:-] Compressed air as per ISO 8573-1:2010 [7:9:-] Inert gas
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Type of mounting	Line installation With accessories Optionally:
Pneumatic connection 1	Internal
Pneumatic connection 2	Internal
Housing material	Die-cast aluminum
Material of bowl	Wrought aluminum alloy