


Branching module MS6N-FRM-3/8-I-Z

Part number: 536983

FESTO



Data sheet

Feature	Value
Mounting position	Any
Structural design	Branching module with non-return function
Operating pressure	0 bar...20 bar
Standard nominal flow rate in main flow direction 1 -> 2	5500 l/min
Standard nominal flow rate outlet at top	2900 l/min
Standard nominal flow rate outlet down	3200 l/min
Operating voltage range AC	0 V...250 V
DC operating voltage range	0 V...125 V
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
For use in the food industry	See supplementary material information
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	400 g
Pneumatic connection 1	3/8 NPT
Pneumatic connection 2	3/8 NPT
Pneumatic connection 3	1/2 NPT
Pneumatic connection 4	1/2 NPT
Note on materials	RoHS-compliant
Housing material	Die-cast aluminum