


Retro-reflective sensor SOEG-RSP-M18-PS-S-2L

Part number: 537699

FESTO



Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Measured variable	Position
Measuring principle	Optoelectronic
Method of measurement	Reflection light barrier
Type of light	Red polarized
Working range	2000 mm
Ambient temperature	-25 °C...55 °C
Switching output	PNP
Switching element function	Dark-switching
Max. switching frequency	1000 Hz
Max. output current	200 mA
Voltage drop	2 V
Short-circuit protection	Pulsed
DC operating voltage range	10 V...36 V
Residual ripple	20 %
Idle current	15 mA
Reverse polarity protection	for all electrical connections
Electrical connection	3-pin M12x1 Plug
Size	M18x1
Type of mounting	With lock nut
Tightening torque	20 Nm
Product weight	53 g
Housing material	Brass Chrome-plated

Feature	Value
Material of union nut	Brass Chrome-plated
Switching status indication	LED yellow
Function reserve indication	LED green
Ambient temperature with flexible cable installation	-5 °C...55 °C
Degree of protection	IP65 IP67
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L