

Muffler expansion

UOMS-1/4

Part number: 538436

FESTO



Data sheet

Feature	Value
Type of seal on screwed plug	without seal
Mounting position	Any
Structural design	Pneumatic muffler, open
Operating pressure of vacuum generator	0 bar...8 bar 0 MPa...0.8 MPa 0 psi...116 psi
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...60 °C
Type of mounting	Engaging
Product weight	8.6 g
Cushioning insert material	PU foam
Material of screwed plug	POM
Housing material	POM
Interior tube material	Wrought aluminum alloy