

Plug socket MSSD-EB-M12

Part number: 539712

FESTO



Data sheet

Feature	Value
Contact durability	50
Type of mounting	On air solenoid valve with M2.5 central screw
Mounting position	Any
Product weight	11 g
Electrical connection	3-pin Socket, angled Form C as per DIN EN 175301-803 Rectangular design
Cable fitting	M12
Approved cable diameter	4 mm...6 mm
Connection cross section	1.5 mm ²
Degree of protection	IP65 as per IEC 60529
Ambient temperature	-40 °C...125 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	PA-reinforced
Seals material	HNBR