



# Throttle plate

## VABF-S4-1-F1B1-C

Part number: 540175

FESTO



### Data sheet

| Feature                                      | Value  |
|--|--|
| Width  | 26 mm  |
| Based on norm                                | ISO 15407-2  |
| Mounting position                            | Any  |
| Operating pressure                           | 1 MPa<br>10 bar  |
| CE marking (see declaration of conformity)   | As per EU low voltage directive                                    |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment                        |
| Operating medium                             | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media     | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)             | 0 - No corrosion stress  |
| LABS (PWIS) conformity                       | VDMA24364-B1/B2-L  |
| Degree of protection                         | IP65<br>NEMA 4   |
| Pilot medium                                 | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Ambient temperature                          | -5 °C...50 °C  |
| Product weight                               | 320 g  |
| Vertical stacking mounting type              | On manifold sub-base<br>On individual sub-base                     |
| Housing material                             | Die-cast aluminum  |