

Pressure gauge kit
DPA-40-10-MA-SET
Part number: 540781

FESTO



Data sheet

Feature	Value
Conforms to standard	EN 837-1
Pressure gauge nominal size	27
Structural design	Bourdon tube pressure gauge
Type of mounting	With external thread
Operating pressure	10 bar
Measurement accuracy class	4
Degree of protection	IP43
Ambient temperature	5 °C...60 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Mounting position	Any
Pneumatic connection	R1/8
Product weight	16 g