

Supply plate
VMPA-FB-SP-7/8-V-4POL
Part number: 541084



Data sheet

Feature	Value
Nominal operating voltage DC	24 V
Permissible voltage fluctuations	+/- 25 %
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65
Ambient temperature	-5 °C...50 °C
Product weight	200 g
Electrical connection	4-pin 7/8" round plug connector
Note on materials	RoHS-compliant
Cover material	PA-reinforced
Housing material	Die-cast aluminum