

Pressure gauge MA-27-16-R1/8

Part number: 541733

FESTO



Data sheet

Feature	Value
Display range	0 bar...16 bar 0 psi...232 psi
Pressure gauge nominal size	27
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Structural design	Bourdon tube pressure gauge
Type of mounting	Line installation
Operating medium	Inert gas Neutral liquids
Information on operating and pilot media	No acetylene No oxygen
Operating pressure	0 MPa...1.6 MPa 0 bar...16 bar 0 psi...232 psi
Intermittent load factor	0.66
Measurement accuracy class	4
Degree of protection	IP43
Temperature of medium	0 °C...60 °C
Ambient temperature	0 °C...60 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Connection position	Centered on rear side
Pneumatic connection	R1/8
Materials in contact with the media	PA-reinforced
Material of screwed plug	PA-reinforced
Housing material	PA
Inspection window material	PS
Housing colour	Black
Product weight	8 g

Feature	Value
Scale	Double scale bar (außen) psi (internal)