

Plastic tubing PEN-8X1,25-SW

Part number: 543242

FESTO



Data sheet

| Feature | Value |
|--|---|
| Outside diameter | 8 mm |
| Bending radius relevant for flow rate | 35 mm |
| Inside diameter | 5.7 mm |
| Min. bending radius | 22.5 mm |
| Tubing characteristics | Suitable for energy chains |
| Temperature-dependent operating pressure | -0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi |
| Information on operating pressure | Water: max. 0.6 MPa at 0 - 50 °C |
| Certification | German Technical Control Board (TÜV) |
| Certificate issuing authority | B 013277 0506 00 |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:::] Water (liquid, ice-free) |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cleanroom class | Statically installed element, no meaningful evaluation possible according to ISO 14644-1 |
| Ambient temperature | -30 °C...60 °C |
| Product weight by length | 0.02327 kg/m |
| Pneumatic connection | For plug connection outside diameter 8 mm For barbed fitting, inside diameter 6 mm, with union nut For barbed fitting, inside diameter 6 mm |
| Color | Black |
| Shore hardness | D 52 +/-3 |
| Note on materials | RoHS-compliant |
| Material of pneumatic tubing | PE |