

# Multi-pin node VABE-S6-1LF-C-M1-C36M

Part number: 543412

FESTO



## Data sheet

| Feature                                      | Value  |
|--|--|
| Based on norm                                | EN 61984   |
| Mounting position                            | Any  |
| Max. no. of valve positions                  | 16 for bistable pneumatic valves<br>32 for monostable pneumatic valves |
| Max. residual current                        | 6 A  |
| Nominal operating voltage DC                 | 24 V   |
| Surge resistance                             | 1.5 kV   |
| Current rating at 40° C                      | 1 A  |
| Contamination level                          | 3  |
| Permissible voltage fluctuations             | +/- 10 %   |
| CE marking (see declaration of conformity)   | As per EU low voltage directive  |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment                            |
| Corrosion resistance class (CRC)             | 0 - No corrosion stress  |
| LABS (PWIS) conformity                       | VDMA24364-B1/B2-L  |
| Degree of protection                         | IP65<br>NEMA 4   |
| Ambient temperature                          | -5 °C...50 °C  |
| Product weight                               | 545 g  |
| Electrical actuation                         | Multi-pin  |
| Electrical connection                        | Socket/terminal strip  |
| Cover material                               | PA   |
| Housing material                             | Die-cast aluminum  |