

Branching module MS4-A-RMV-IPM-80

Part number: 543500

FESTO



Data sheet

Feature	Value
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C...60 °C
Product weight	150 g
Note on materials	RoHS-compliant
Material of sub-base	Die-cast aluminum
Seals material	NBR
Hollow bolt material	Die-cast aluminum
Module connector material	Die-cast aluminum
Material of screws	Steel