

Adapter
AD-G1-1NPT-I
Part number: 546546



Data sheet

Feature	Value
Nominal width	21.4 mm
Operating pressure for entire temperature range	-0.95 bar...10 bar
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Max. tightening torque, pneumatic connection 1	90 Nm
Max. tightening torque, pneumatic connection 2	35 Nm
Product weight	212.68 g
Pneumatic connection 1	External thread, G1
Pneumatic connection 2	Female thread 1 NPT
Note on materials	RoHS-compliant
Seals material	PVC
Housing material	Steel, galvanized