

Adapter

NEFC-M12G5-0.3-U1G5

Part number: 547432



Data sheet

Feature	Value
Type of mounting	Screw-in
Electrical connection	5-pin M12x1 Plug
Cable length	0.3 m
Cable design	4 x 0.34 mm ²
Degree of protection	IP20
Ambient temperature	-5 °C...50 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	0 - No corrosion stress
Material of cable sheath	PUR
Housing material	ABS
Material of pin contacts	Brass, gold-plated