

Vacuum generator cartridge VN-05-L

Part number: 547694

FESTO



Data sheet

| Feature | Value |
|---|---|
| Nominal width of Laval nozzle | 0.45 mm |
| Mounting position | Any |
| Ejector characteristics | Standard High suction volume |
| Operating pressure | 1 bar...8 bar |
| Nominal operating pressure | 6 bar |
| Max. suction rate with respect to atmosphere | 13.6 l/min |
| Air supply time at nominal operating pressure | 2.04 s |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication not possible |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | 0 °C...60 °C |
| Ambient temperature | 0 °C...60 °C |
| Product weight | 0.65 g |
| Seals material | NBR |
| Female nozzle material | POM |
| Material of jet nozzle | Wrought aluminum alloy |