

Vacuum generator cartridge VN-20-L

Part number: 547702

FESTO



Data sheet

Feature	Value
Nominal width of Laval nozzle	2 mm
Mounting position	Any
Ejector characteristics	Standard High suction volume
Operating pressure	1 bar...8 bar
Nominal operating pressure	6 bar
Max. suction rate with respect to atmosphere	184.4 l/min
Air supply time at nominal operating pressure	0.17 s
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	0 °C...60 °C
Ambient temperature	0 °C...60 °C
Product weight	3.75 g
Seals material	NBR
Female nozzle material	POM
Material of jet nozzle	Wrought aluminum alloy