

Pneumatic shock absorber DYEF-M10-Y1F

Part number: 548374

FESTO



Data sheet

Feature	Value
Size	M10
Stroke	3.7 mm
Cushioning	Elastic cushioning rings/pads at both ends with metallic fixed stop
Mounting position	Any
Position sensing	None
Max. impact velocity	0.8 m/s
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C...60 °C
Cushioning length	3.7 mm
Max. energy absorption per stroke	0.06 J
Product weight	19.7 g
Type of mounting	With lock nut
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	High-alloy steel