

Cover
VAEM-S6-C-S6-R5

Part number: 549048

FESTO



Data sheet

Feature	Value
Max. no. of valve positions	12 for monostable pneumatic valves 6 for bistable pneumatic valves
Max. residual current	10 A
Nominal operating voltage DC	24 V
Permissible voltage fluctuations	+/- 10 %
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C...50 °C
Product weight	200 g
Number of electrical connections	6
Electrical connection	5-pin M12 Plug
Housing material	PA