

Connection block CPE14-PRS-3/8-8-NPT

Part number: 550085

FESTO



Data sheet

| Feature | Value |
|---|--|
| Width dimension | 20 mm |
| Mounting position | Any |
| Max. no. of valve positions | 8 |
| Max. no. of pressure zones | 2 |
| Burst pressure | 5 MPa 50 bar 725 psi |
| Operating pressure | -0.09 MPa...1 MPa -0.9 bar...10 bar |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | 23 °F...122 °F |
| Ambient temperature | 23 °F...122 °F |
| Max. tightening torque for valve mounting | 0.9 ft-lbf |
| Product weight | 26.5 oz |
| Manifold block type of mounting | With through-hole |
| Pneumatic valve mounting type | With internal thread |
| Pneumatic connection 1 | 3/8 NPT |
| Pneumatic connection 3 | 3/8 NPT |
| Pneumatic connection 5 | 3/8 NPT |
| Note on materials | RoHS-compliant |
| Manifold rail material | Wrought aluminum alloy |