

# Plug socket with cable KMYZ-4-5,0-B-EX

Part number: 550482

FESTO



## Data sheet

Feature	Value
Maritime classification	See certificate
Type of mounting	On air solenoid valve with M2 central screw
Mounting position	Any
Product weight	62.5 g
Electrical connection	Socket, angled Cable Rectangular design MSZB
DC operating voltage range	3 V...36 V
Nominal operating voltage DC	24 V
Current rating at 40° C	1 A
Surge resistance	900 V
Protective earth connection	Not available
Cable length	5 m
Cable characteristic	Standard
Cable design	2 x 0.35 mm <sup>2</sup>
Degree of protection	IP40
Ambient temperature	-10 °C...50 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	1 - Low corrosion stress
Material of cable sheath	PVC
Housing material	PA
Material of pin contacts	Bronze