

Connection block CPE10-3/2-PRS-1/4-2

Part number: 550550

FESTO



Data sheet

Feature	Value
Width dimension	16 mm
Mounting position	Any
Max. no. of valve positions	2
Max. no. of pressure zones	2
Burst pressure	5 MPa 50 bar 725 psi
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-5 °C...50 °C
Ambient temperature	-5 °C...50 °C
Max. tightening torque for valve mounting	1.2 Nm
Product weight	128 g
Manifold block type of mounting	With through-hole
Pneumatic valve mounting type	With internal thread
Pneumatic connection 1	G1/4
Pneumatic connection 3	G1/4
Pneumatic connection 5	G1/4
Note on materials	RoHS-compliant
Manifold rail material	Wrought aluminum alloy