


Gearbox
EMGA-60-P-G5-SAS-70
Part number: 552191

FESTO



Data sheet

Feature	Value
Gearbox flange size	60 mm
Motor flange size	70 mm
Torsional backlash	0.17 deg
Gearbox type	Planetary gear
Gear ratio	5:1
Max. actuator speed	13000 rpm
Gearbox operating temperature	-25 °C...90 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP54
Continuous output torque	22 Nm
Mass moment of inertia, gearbox	0.078 kgcm ²
Max. output torque	35.2 Nm
Max. efficiency	98 %
Torsional rigidity	2.3 Nm/arcmin
Product weight	900 g
Gearbox interface, output shaft	60G
Gearbox interface, actuator	70A
Note on materials	RoHS-compliant