

Adapter lens
SASF-L1-LS2-M4
Part number: 552831



Data sheet

Feature	Value
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP66
Ambient temperature	-30 °C...150 °C
Tightening torque	-0.2 Nm...0.6 Nm
Product weight	0.7 g
Lens function	Focusing Light spot diameter 0.7 mm at a distance of 10 mm Depending on fiber-optic cable
Housing material	Aluminum Anodized