

# Bellows kit

## DADB-V6-40-S376-425

Part number: 553305

FESTO



## Data sheet

Feature	Value
Outside diameter	46 mm
Size	40
Stroke range	376 mm...425 mm
Piston rod extension	115 mm
Design	Round
Mounting position	Any
Structural design	Bellows kit with ducted exhaust air
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Media resistance	Stäube Chips Oils Grease Petrol
Degree of protection	IP54
Ambient temperature	-10 °C...80 °C
Product weight	129 g
Type of mounting	Push-on With threaded pin
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Adaption parts material	PA-reinforced
Seals material	NBR
Bellows material	NBR
Threaded pin material	High-alloy stainless steel