

Bellows kit DADB-V6-80-S426-475

Part number: 553367

FESTO



Data sheet

| Feature | Value |
|----------------------------------|---|
| Outside diameter | 93 mm |
| Size | 80 |
| Stroke range | 426 mm...475 mm |
| Piston rod extension | 110 mm |
| Design | Round |
| Mounting position | Any |
| Structural design | Bellows kit with ducted exhaust air |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Media resistance | Stäube Chips Oils Grease Petrol |
| Degree of protection | IP54 |
| Ambient temperature | -10 °C...80 °C |
| Product weight | 334 g |
| Type of mounting | Push-on With threaded pin |
| Pneumatic connection | G1/4 |
| Note on materials | RoHS-compliant |
| Adaption parts material | PA-reinforced |
| Seals material | NBR |
| Bellows material | NBR |
| Threaded pin material | High-alloy stainless steel |