

# Proximity sensor SIEF-M18B-NS-S-L

Part number: 553547

FESTO



## Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU low voltage directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions To UK instructions for electrical equipment
Note on materials	RoHS-compliant
Rated operating distance	5 mm
Ambient temperature	-30 °C...85 °C
Repetition accuracy	0.28 mm
Switching output	NPN
Switching element function	N/O contact
Max. switching frequency DC	3000 Hz
Max. output current	200 mA
Short-circuit protection	Pulsed
DC operating voltage range	10 V...30 V
Reverse polarity protection	for all electrical connections
Electrical connection	3-pin M12x1 Plug
Material of plug housing	Brass Chrome-plated
Size	M18
Mounting type	Flush
Product weight	41 g
Housing material	Brass Chrome-plated
Switching status indication	LED yellow
Degree of protection	IP68
Resistance to interference from magnetic fields	Magnetic direct and alternating fields

Feature	Value
Surge resistance	0.8 kV
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Contamination level	3
Selection of additional sensor information	with reduction factor 1 – resistance to magnetic fields
Selection of sensor version	Standard