

Plastic tubing PAN

Part number: 553610

FESTO



Data sheet

Feature	Value
Outside diameter	4 mm...16 mm
Inside diameter	2.5 mm...12 mm
Conforms to standard	DIN 73378-PA12-PHL
Temperature-dependent operating pressure	-0.95 bar...35 bar
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0527 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-] Mineral oil
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom suitability, measured according to ISO 14644-14	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
Ambient temperature	-60 °C...100 °C
Color	Blue Brown Yellow Green Natural Red Black Silver White
Note on materials	RoHS-compliant
Material of pneumatic tubing	PA12-P TPE-A