

Plastic tubing PLN

Part number: 553850

FESTO



Data sheet

Feature	Value
Outside diameter	4 mm...16 mm
Inside diameter	2.9 mm...12 mm
Temperature-dependent operating pressure	-0.95 bar...14 bar
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-] Water (liquid, ice-free)
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
For use in the food industry	See supplementary material information
Ambient temperature	-30 °C...80 °C
Color	Blue Brown Yellow Green Natural Red Black Silver White
Note on materials	RoHS-compliant
Material of pneumatic tubing	PE