

Plastic tubing PAN-10X1,5-SW

Part number: 553915

FESTO



Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	58 mm
Inside diameter	7 mm
Min. bending radius	27 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 MPa...1.7 MPa -0.95 bar...17 bar -13.775 psi...246.5 psi
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-30 °C...80 °C
Product weight by length	0.042 kg/m
Pneumatic connection	For plug connection outside diameter 10 mm
Color	Black
Shore hardness	D 55 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	TPE-A