

## Sub-base VABS-S2-2S-G12-C1

Part number: 555638

**FESTO**



## Data sheet

| Feature                                  | Value  |
|--|--|
| Width                                    | 52 mm  |
| Based on norm                            | ISO 5599-2   |
| Mounting position                        | Any  |
| Pilot air supply port                    | External   |
| Operating pressure                       | -0.09 MPa...1 MPa<br>-0.9 bar...10 bar                             |
| Operating voltage range AC               | 110 V  |
| DC operating voltage range               | 24 V   |
| Surge resistance                         | 4 kV   |
| Current rating at 40° C                  | 2 A  |
| Contamination level                      | 3  |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 0 - No corrosion stress  |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Degree of protection                     | IP65<br>NEMA 4<br>In mounted state                                 |
| Ambient temperature                      | -5 °C...50 °C  |
| Product weight                           | 815 g  |
| Connection cross section                 | 0.08 mm <sup>2</sup> ...0.75 mm <sup>2</sup>                       |
| Type of mounting                         | With through-hole  |
| Note on materials                        | RoHS-compliant   |
| Material of sub-base                     | Cast aluminum  |