

Plug
CAMF-B-M25-G4
Part number: 555676



Data sheet

Feature	Value
Additional functions	Mounting to prevent loss
Mounting position	Any
Nominal operating voltage DC	24 V
Operating voltage range AC	160 V
Current rating	1 A
Degree of protection	IP65 as per IEC 60529
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	0 - No corrosion stress