


Vertical pressure shut-off plate VABF-S2-2-L1D1-C

Part number: 555791

FESTO



Data sheet

Feature	Value
Width	54 mm
Based on norm	ISO 5599-2
Mounting position	Any
Pneumatic vertical stacking	Shut-off for 1
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Inlet pressure 1	0.5 bar...10 bar
Inlet pressure 1 MPa	0.05 MPa...1 MPa
Inlet pressure 1 psi	7.25 psi...145 psi
Standard nominal flow rate	1950 l/min
CE marking (see declaration of conformity)	As per EU low voltage directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C...50 °C
Product weight	1030 g
Vertical stacking mounting type	On manifold sub-base On individual sub-base
Note on materials	RoHS-compliant
Housing material	Die-cast aluminum