

Drive shaft adapter
EAMB-24-6-15X21-16X20
Part number: 558036

FESTO



Data sheet

Feature	Value
Diameter of holder 1	15 mm
Diameter of holder 2	16 mm
Size	80
Nominal length	21 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	3.1 kgmm ²
Transferable torque	29 Nm
Product weight	68 g
Note on materials	RoHS-compliant