

Plastic tubing PLN-16X2-SI

Part number: 558216

FESTO



Data sheet

Feature	Value
Outside diameter	16 mm
Bending radius relevant for flow rate	95 mm
Inside diameter	12 mm
Min. bending radius	55 mm
Temperature-dependent operating pressure	-0.095 MPa...1.4 MPa -0.95 bar...14 bar -13.775 psi...203 psi
Information on operating pressure	Water: max. 0.6 MPa at 0 - 50 °C
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
For use in the food industry	See supplementary material information
Ambient temperature	-30 °C...80 °C
Product weight by length	0.082 kg/m
Pneumatic connection	For plug connection outside diameter 16 mm
Color	Silver
Note on materials	RoHS-compliant
Material of pneumatic tubing	PE