

Push-in T-fitting NPQM-T-G38-Q12-P10

Part number: 558745

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal width | 11 mm |
| Type of seal on screwed plug | Sealing ring |
| Design | T-shape |
| Pack size | 10 |
| Structural design | Push-pull principle |
| Operating pressure for entire temperature range | -0.095 MPa...1.6 MPa -0.95 bar...16 bar -13.775 psi...232 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:::] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C...70 °C |
| Nominal tightening torque | 9 Nm |
| Tolerance for nominal tightening torque | ± 20% |
| Product weight | 75.3 g |
| Type of mounting | External hexagon, AF 20 |
| Pneumatic connection 1 | External thread G3/8 |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 12 mm |
| Note on materials | RoHS-compliant |
| Housing material | Brass, nickel-plated |
| Material of tubing seal | NBR |