

# Push-in connector NPQM-D-Q12-E-P10

Part number: 558764

**FESTO**



## Data sheet

| Feature   | Value   |
|---|---|
| Size  | Standard  |
| Nominal width                                   | 11 mm   |
| Design  | Straight design   |
| Pack size                                       | 10  |
| Structural design                               | Push-pull principle   |
| Operating pressure for entire temperature range | -0.095 MPa...1.6 MPa<br>-0.95 bar...16 bar<br>-13.775 psi...232 psi |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7::-]                        |
| Information on operating and pilot media        | Operation with oil lubrication possible                             |
| Corrosion resistance class (CRC)                | 1 - Low corrosion stress  |
| LABS (PWIS) conformity                          | VDMA24364-B1/B2-L   |
| Ambient temperature                             | -20 °C...70 °C  |
| Product weight                                  | 36.6 g  |
| Pneumatic connection 1                          | for pneumatic tubing outside diameter 12 mm                         |
| Pneumatic connection 2                          | for pneumatic tubing outside diameter 12 mm                         |
| Note on materials                               | RoHS-compliant  |
| Housing material                                | Brass, nickel-plated  |
| Material of tubing seal                         | NBR   |