

Push-in sleeve NPQM-D-S12-E-P10

Part number: 558815

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	10 mm
Operating pressure for entire temperature range	-0.095 MPa...1.6 MPa -0.95 bar...16 bar -13.775 psi...232 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...70 °C
Product weight	14 g
Pneumatic connection 1	Push-in sleeve QS-12
Pneumatic connection 2	Push-in sleeve QS-12
Note on materials	RoHS-compliant
Housing material	Brass, nickel-plated