

**Hood**  
**VMPAL-KM-SD25-IP67-0**  
Part number: 560428



**Data sheet**

Feature	Value
Product weight	100 g
Electrical connection	Customizable
Approved cable diameter	5 mm...13 mm
Connection cross section	0.2 mm²...0.5 mm²
Degree of protection	IP67 as per IEC 60529
Ambient temperature	-5 °C...80 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	2 - Moderate corrosion stress