

Manifold subbase VABV-S2-2S-N12-T2

Part number: 560843

FESTO



Data sheet

| Feature | Value |
|--|---|
| Width dimension | 59 mm |
| Valve terminal type | 44 |
| Operating pressure | -0.09 MPa...1 MPa -0.9 bar...10 bar |
| CE marking (see declaration of conformity) | As per EU low voltage directive |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 610 g |
| Pneumatic connection 2 | 1/2 NPT |
| Pneumatic connection 4 | 1/2 NPT |
| Note on materials | RoHS-compliant |
| Plate material | Die-cast aluminum |