

# Manifold subbase VABV-S2-2S-N12-T1

Part number: 560844

FESTO



## Data sheet

Feature	Value
Width dimension	59 mm
Valve terminal type	44
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
CE marking (see declaration of conformity)	As per EU low voltage directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	610 g
Pneumatic connection 2	1/2 NPT
Pneumatic connection 4	1/2 NPT
Note on materials	RoHS-compliant
Plate material	Die-cast aluminum