


**Sub-base**  
**VMPAL-AP-20-QS10-1-T1**  
Part number: 561015

**FESTO**



**Data sheet**

Feature	Value
Width	21.2 mm
Length	107.3 mm
Width dimension	21.2 mm
Valve size	20 mm
Pressure zone separation	Channel 1
Max. no. of valve positions	1
Flow direction	Reversible
Valve manifold design	Valve sizes can be mixed
Max. no. of solenoid coils	1
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Pilot pressure MPa	0.3 MPa...0.8 MPa
Pilot pressure	3 bar...8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C...50 °C
Product weight	82.28 g
Pneumatic connection 2	for pneumatic tubing outside diameter 10 mm
Pneumatic connection 4	For pneumatic tubing outside diameter 10 mm
Note on materials	RoHS-compliant
Material of sub-base	PA-reinforced