

Sub-base
VMPAL-AP-4X14-QS1/4"-1
 Part number: 561103

FESTO



Data sheet

Feature	Value
Width	59.6 mm
Length	107.3 mm
Width dimension	14.9 mm
Valve size	14 mm
Max. no. of valve positions	4
Flow direction	Reversible
Valve manifold design	Valve sizes can be mixed
Max. no. of solenoid coils	4
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Pilot pressure MPa	0.3 MPa...0.8 MPa
Pilot pressure	3 bar...8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C...50 °C
Product weight	130.8 g
Pneumatic connection 2	for pneumatic tubing outer diameter 1/4"
Pneumatic connection 4	For pneumatic tubing outside diameter 1/4"
Note on materials	RoHS-compliant
Material of sub-base	PA-reinforced