

**Distributor**  
**FR-4-3/8**  
Part number: 561602

**FESTO**



**Data sheet**

Feature	Value
Nominal width	16 mm
Mounting position	Any
Operating pressure for entire temperature range	0 bar...16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
No. of outlets	3
No. of supply lines	1
Pneumatic connection 1	G3/8
Pneumatic connection 2	G3/8
Housing material	Wrought aluminum alloy Anodized