

Quick coupling
EAMC-16-20-5-5
Part number: 562676

FESTO



Data sheet

Feature	Value
Diameter of holder 1	5 mm
Diameter of holder 2	5 mm
Size	16
Nominal length	20 mm
Mounting position	Any
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	0.28 kgmm ²
Transferable torque	1.1 Nm
Product weight	8 g
Note on materials	RoHS-compliant