

**Adapter**  
**NPFV-AF-G14-N14-MF**  
Part number: 563397



**Data sheet**

| Feature                             | Value                                                              |
|-------------------------------------|--------------------------------------------------------------------|
| Nominal width                       | 6 mm                                                               |
| Operating pressure                  | 0.2 MPa...0.8 MPa<br>2 bar...8 bar                                 |
| Explosion prevention and protection | Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX) |
| Corrosion resistance class (CRC)    | 1 - Low corrosion stress                                           |
| LABS (PWIS) conformity              | VDMA24364 zone III                                                 |
| Pneumatic connection 1              | G1/4                                                               |
| Pneumatic connection 2              | 1/4 NPT                                                            |
| Note on materials                   | RoHS-compliant                                                     |
| Adapter material                    | High-alloy stainless steel                                         |
| Seals material                      | NBR                                                                |