

# Push-in fitting QBF-1/4-5/32-U

Part number: 564642

FESTO



## Data sheet

Feature	Value
Size	Standard
Nominal width	0.138 in
Type of seal on screwed plug	Coating
Mounting position	Any
Design	Straight design
Pack size	10
Structural design	Push-pull principle
Operating pressure for entire temperature range	0.095 MPa...1 MPa 0.95 bar...10 bar 13.775 psi...145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	0 °C...60 °C
Max. tightening torque	8.85 ft-lbf
Product weight	0.698 oz
Type of mounting	External hexagon 11/16
Pneumatic connection 1	Internal thread 1/4 NPT
Pneumatic connection 2	for pneumatic tubing outside diameter 5/32"
Ambient temperature Fahrenheit	32 °F...140 °F
Releasing ring color	Gray
Note on materials	RoHS-compliant
Housing material	Brass, nickel-plated
Material of threaded seal	PTFE
Releasing ring material	POM
Material of tubing seal	NBR
Material of tube retaining claw	High-alloy stainless steel