

Multiple distributor QBT3-1/4T-5/32-U

Part number: 564791

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Standard |
| Nominal width | 0.126 in |
| Mounting position | Any |
| Structural design | Push-pull principle |
| Operating pressure for entire temperature range | 0.095 MPa...1 MPa 0.95 bar...10 bar 13.775 psi...145 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7::-] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Ambient temperature | 0 °C...60 °C |
| Max. tightening torque | 8.85 ft-lbf |
| Product weight | 0.85 oz |
| Pneumatic connection 1 | For pneumatic tubing outside diameter 1/4" |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 5/32" |
| Ambient temperature Fahrenheit | 32 °F...140 °F |
| Releasing ring color | Gray |
| Note on materials | RoHS-compliant |
| Housing material | PBT |
| Releasing ring material | POM |
| Material of tubing seal | NBR |
| Material of tube retaining claw | High-alloy stainless steel |