

Plastic tubing
PAN-MF-10X1,25-SW
Part number: 570360

FESTO



Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	65 mm
Inside diameter	7.5 mm
Min. bending radius	45 mm
Conforms to standard	DIN 73378-PA12-PHL
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 MPa...1.9 MPa -0.95 bar...19 bar -13.775 psi...275.5 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::] Mineral oil
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-60 °C...100 °C
Product weight by length	0.035 kg/m
Pneumatic connection	For plug connection outside diameter 10 mm
Color	Black
Shore hardness	D 65 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	PA12-P